



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR175VBUPA *Delisted* 175W P/S MH Vert Base Up Burn Lamp

Ge By Current Lamps

Catalog Number	MVR175VBUPA
Manufacturer	Ge By Current Lamps
Description	Ge Multi-Vapor®, 12622, 175 WTT, 17500 LM, 4000 KV, 75 Cri, Mogul Screw (E39) Base, 15000 HR Average Life
Weight per unit	0.4800 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

average life	15000.0
Base	Mogul Screw (E39)
lumens	17500.0
Wattage	175.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	75.0
color temperature	4000.0
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	*DELISTED* 175W P/S MH VERT BASE UP BURN LAMP
extra long description	GEL MVR175/VBU/PA 12622 MULTIVAPOR
Long Description	GE Multi-Vapor®, 12622, 175 WTT, 17500 LM, 4000 KV, 75 CRI, Mogul Screw (E39) Base, 15000 HR Average Life
Product Type	12622 Multivapor
Special Features	7.5IN Length

Manufacturer Information

Brand	GE Current
GTIN	00043168126229
Manufacturers Part Number	MVR175/VBU/PA
UPC	043168126229

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.48

Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------