



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR250U 250W ED28 Metal Halide Clear Mogul Base Lamp

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | MVR250U |
| Manufacturer | Ge By Current Lamps |
| Description | Metal Halide Lamp, 65, 4200 K, 19100 LM (Horizontal);20800 LM (Vertical) Brightness (Lumens), 250 W, Clear, Hard Glass Material, 6000 H (Horizontal);10000 H (Vertical) Average Life, Mogul Base, M58 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 31 % Mercury Content, 5.55 LB |
| Weight per unit | 0.4600 (lbs/each) |
| Product Category | Hid Quartz Metal Halide Lamps |

Features

| | |
|---------|-------------------|
| Base | Mogul Screw (E39) |
| Wattage | 250 |

Material, Color, and Finish

| | |
|-----------------------------|------------------------|
| Color | Clear |
| color rendering index (cri) | 65 |
| Style | Enclosed fixtures only |

Descriptions

| | |
|------------------------|--|
| Description | 250W ED28 METAL HALIDE CLEAR MOGUL BASE LAMP |
| extra long description | GEL MVR250/U 42729 MULTIVAPOR |
| Special Features | 8.25IN Length |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168427296 |
| UPC | 043168427296 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.46 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|