



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR250UPA 250W P/S Metal Halide Universal Burn Lamp

Ge By Current Lamps

Catalog Number	MVR250UPA
Manufacturer	Ge By Current Lamps
Description	Ge Multi-Vapor®, 78665, 250 WTT, 3900 KV, 62 Cri, Mogul Screw (E39) Base
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
Wattage	250.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	62.0
color temperature	3900.0
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	250W P/S METAL HALIDE UNIVERSAL BURN LAMP
extra long description	GEL MVR250/U/PA 78665 MULTIVAPOR
Long Description	GE Multi-Vapor®, 78665, 250 WTT, 3900 KV, 62 CRI, Mogul Screw (E39) Base
Product Type	78665 Multivapor
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168786652
Manufacturers Part Number	MVR250/U/PA
UPC	043168786652

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------