



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR250VBUPA *Delisted* 250W PS/MH Mog Vert Base Up Burn Pos

Ge By Current Lamps

Catalog Number	MVR250VBUPA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4200 K, 23000 LM Brightness (Lumens), 250 W, Clear, Hard Glass Material, 15000 H Average Life, Mogul Base, M138/M153 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 27 % Mercury Content, 5.37 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
lumens	23000
Wattage	250

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	*DELISTED* 250W PS/MH MOG VERT BASE UP BURN POS
Special Features	8.25IN Length

Manufacturer Information

Brand	GE Current
GTIN	00043168263177
UPC	043168263177

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------