



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR250VBUPA \*Delisted\* 250W PS/MH Mog Vert Base Up Burn Pos

*Ge By Current Lamps*

Catalog Number	MVR250VBUPA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4200 K, 23000 LM Brightness (Lumens), 250 W, Clear, Hard Glass Material, 15000 H Average Life, Mogul Base, M138/M153 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 27 % Mercury Content, 5.37 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
lumens	23000
Wattage	250

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Enclosed fixtures only

### Descriptions

Description	*DELISTED* 250W PS/MH MOG VERT BASE UP BURN POS
Special Features	8.25IN Length

### Manufacturer Information

Brand	GE Current
GTIN	00043168263177
UPC	043168263177

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Availability

Manufacturer Status	Inactive
---------------------	----------

### Packaging

Carton	1
Package	12
Weight Per each	0.46

### Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------