



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR320VBUH0PA 320W ED28 Metal Halide Clear Mogul Base Pulserc

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | MVR320VBUH0PA |
| Manufacturer | Ge By Current Lamps |
| Description | Metal Halide Lamp, 65, 4000 K, 31000 LM Brightness (Lumens), 320 W, Clear, Hard Glass Material, 20000 H Average Life, Mogul Base, M132/M154 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 30 % Mercury Content, 5.33 LB |
| Weight per unit | 0.4600 (lbs/each) |
| Product Category | Hid Quartz Metal Halide Lamps |

Features

| | |
|---------|-------------------|
| Base | Mogul Screw (E39) |
| lumens | 31000 |
| Wattage | 320 |

Material, Color, and Finish

| | |
|-----------------------------|------------------------|
| Color | Clear |
| color rendering index (cri) | 65 |
| Finish | Clear |
| Style | Enclosed fixtures only |

Descriptions

| | |
|------------------------|---|
| Description | 320W ED28 METAL HALIDE CLEAR MOGUL BASE PULSERC |
| extra long description | GEL MVR320/VBU/HO/PA 27501 MULTIVAP |
| Special Features | 8.25IN Length |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168275019 |
| UPC | 043168275019 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.46 |

Uses, Certifications, and Standards

| | |
|-------------|-------------------------|
| Application | Vertical base up +/-15° |
|-------------|-------------------------|