



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR320VBUH0PA 320W ED28 Metal Halide Clear Mogul Base Pulserc

*Ge By Current Lamps*

Catalog Number	MVR320VBUH0PA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 31000 LM Brightness (Lumens), 320 W, Clear, Hard Glass Material, 20000 H Average Life, Mogul Base, M132/M154 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 30 % Mercury Content, 5.33 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
lumens	31000.0
Wattage	320.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Finish	Clear
Style	Enclosed fixtures only

### Descriptions

Description	320W ED28 METAL HALIDE CLEAR MOGUL BASE PULSERC
extra long description	GEL MVR320/VBU/HO/PA 27501 MULTIVAP
Special Features	8.25IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168275019
UPC	043168275019

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	12
Weight Per each	0.46

### Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------