



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR400CU \*Delisted\* 400W ED37 MH Coated Mogul Base Lamp

*Ge By Current Lamps*

Catalog Number	MVR400CU
Manufacturer	Ge By Current Lamps
Description	Ge Multi-Vapor®, 43829, 400 WTT, 3700 KV, 70 Cri, Mogul Screw (E39) Base
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
Wattage	400.0

### Material, Color, and Finish

Color	COATED
color rendering index (cri)	70.0
color temperature	3700.0
Finish	COATED
Style	Open Fixture-Restricted Position (S-Rated)

### Descriptions

Description	*DELISTED* 400W ED37 MH COATED MOGUL BASE LAMP
extra long description	GEL MVR400/C/U 43829 MULTIVAPOR
Long Description	GE Multi-Vapor®, 43829, 400 WTT, 3700 KV, 70 CRI, Mogul Screw (E39) Base
Product Type	43829 Multivapor
Special Features	11.5IN Length

### Manufacturer Information

Brand	GE Current
GTIN	00043168438292
Manufacturers Part Number	MVR400/C/U
UPC	043168438292

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.74

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------