



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR400H0RED28PA MH Lamp

Ge By Current Lamps

Catalog Number	MVR400H0RED28PA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4100 K, 38000 LM Brightness (Lumens), 400 W, Clear, Hard Glass Material, 20000 H Average Life, E39 Mogul Screw Base, M135/M155 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 40 % Mercury Content, 5.91 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
lumens	38000
Wattage	400

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	MH LAMP
extra long description	GEL MVR400HOR/ED28PA 72885 MULTIVAP
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168728850
Manufacturers Part Number	MVR400HOR/ED28PA
UPC	043168728850

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Horizontal +/-75°
-------------	-------------------