



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR400U **\*\*Delisted\*\*** 400W ED37 Metal Halide Clear Mog Base

*Ge By Current Lamps*

Catalog Number	MVR400U
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 33100 LM (Horizontal);36000 LM (Vertical) Brightness (Lumens), 400 W, Clear, Hard Glass Material, 15000 H (Horizontal);20000 H (Vertical) Average Life, Mogul Base, M59 Ansi Ballast Code, Non Dimmable, 4.62 In Diameter, 11.5 In Height, 61.11 % Mercury Content, 4.45 LB
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
Wattage	400

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Style	Open Fixture-Restricted Position (S-Rated)

### Descriptions

Description	<b>**DELISTED**</b> 400W ED37 METAL HALIDE CLEAR MOG BASE
extra long description	GEL MVR400/U 43828 MULTIVAPOR
Special Features	11.5IN Length

### Manufacturer Information

Brand	GE Current
GTIN	00043168438285
UPC	043168438285

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.74