



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR400VBUED28PA 400W PS/MH ED28 Clear Bulb Mog Screw Base 4000K La *Ge By Current Lamps*

Catalog Number	MVR400VBUED28PA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 44000 LM Brightness (Lumens), 400 W, Clear, Hard Glass Material, 20000 H Average Life, Mogul Base, M135/M155 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 41.5 % Mercury Content, 5.79 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
lumens	44000
Wattage	400

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	400W PS/MH ED28 CLEAR BULB MOG SCREW BASE 4000K LA
extra long description	GEL MVR400/VBUED28PA 46271 MULTIVAP
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168462716
UPC	043168462716

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------