



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR70UMED 70W BD17 Metal Halide Clear Med Base Lamp

*Ge By Current Lamps*

Catalog Number	MVR70UMED
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 5500 LM Brightness (Lumens), 70 W, Clear, Hard Glass Material, 12000 H Average Life, Medium Base, M98 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.43 In Height, 4.9 % Mercury Content, 2.0 LB
Weight per unit	0.3300 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Medium Screw (E26)
lumens	5500.0
Voltage Rating	85.0
Wattage	70.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Style	Enclosed fixtures only

### Descriptions

Description	70W BD17 METAL HALIDE CLEAR MED BASE LAMP
extra long description	GEL MVR70/U/MED 12590 MULTIVAPOR
Special Features	5.43IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168125901
UPC	043168125901

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.33