



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR70UMED 70W BD17 Metal Halide Clear Med Base Lamp

Ge By Current Lamps

Catalog Number	MVR70UMED
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 5500 LM Brightness (Lumens), 70 W, Clear, Hard Glass Material, 12000 H Average Life, Medium Base, M98 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.43 In Height, 4.9 % Mercury Content, 2.0 LB
Weight per unit	0.3300 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Medium Screw (E26)
lumens	5500
Voltage Rating	85
Wattage	70

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Style	Enclosed fixtures only

Descriptions

Description	70W BD17 METAL HALIDE CLEAR MED BASE LAMP
extra long description	GEL MVR70/U/MED 12590 MULTIVAPOR
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168125901
UPC	043168125901

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.33