



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MXR150UMEDO 150W or PS/MH Med Screw Universal Burn Position

*Ge By Current Lamps*

Catalog Number	MXR150UMEDO
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 70, 3500 K, 12500 LM Brightness (Lumens), 150 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M102 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 11.4 % Mercury Content, 1.78 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Medium Screw (E26)
lumens	12500.0
Wattage	150.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	70.0
Finish	Clear
Style	Open or enclosed fixtures

### Descriptions

Description	150W OR PS/MH MED SCREW UNIVERSAL BURN POSITION
extra long description	GEL MXR150/U/MED/O 45683 MULTIVAPOR
Special Features	5.43IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168456838
Manufacturers Part Number	MXR150/U/MED/O
UPC	043168456838

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.3

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------