



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MXR70UMEDO 70W or PS/MH Med Screw Universal Burn Position

Ge By Current Lamps

Catalog Number	MXR70UMEDO
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 70, 3200 K, 5500 LM Brightness (Lumens), 70 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M98 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 4.02 % Mercury Content, 1.78 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Medium Screw (E26)
lumens	5500.0
Wattage	70.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	70.0
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	70W OR PS/MH MED SCREW UNIVERSAL BURN POSITION
extra long description	GEL MXR70/U/MED/O 12377 MULTIVAPOR
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168123778
UPC	043168123778

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------