



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NON25 25A 250V One-Time Class K5 Fuse

Bussmann Fuses

Catalog Number	NON25
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Non Fuse, Non Current Limiting, Light Duty Circuit Locations, 25 A, Class H, Non-Indicating, Ferrule End X Ferrule End, 50 Kaic At 125 VDC, 50 Kaic At 250 Vac, Standard, 10, 250 V, 125 VDC
Weight per unit	0.0400 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

amperage rating	25
class	Class H
connection	Ferrule End X Ferrule End
dimensions	2.0000 IN X 0.5600 IN X 0.5600 IN
interrupt rating	50
media	Yes
Voltage Rating	250 VAC, 125 VDC

Dimensions and Weight

Size	0.56 In Diameter X 2.00 In Length
------	-----------------------------------

Descriptions

Description	25A 250V ONE-TIME CLASS K5 FUSE
extra long description	BUSS NON-25 BUSS ONE TIME FUSE
Features	Basic Protection 250Vac (NON) and 600Vac (NOS), 1/8a -600A General Purpose One-time fuses
Long Description	Eaton Bussmann series NON fuse, Non current limiting, Light duty circuit locations, 25 A, Class H, Non-indicating, Ferrule end x ferrule end, 50 kAIC at 125 Vdc, 50 kAIC at 250 Vac, Standard, 10, 250 V, 125 Vdc
Product Type	Buss One Time Fuse
Special Features	Non current limiting

Manufacturer Information

Brand	Eaton
GTIN	00051712101585
Manufacturers Part Number	NON-25
UPC	051712101585

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked