


## All Purpose Type Split Bolts - N-1/0SP

<b>Drawn - SD</b>	
<b>Approved - KM</b>	
<b>Material - Copper / Finish: Tin Plated</b>	
<b>Title - All Purpose Type Split Bolts</b>	
	
<b>Max Run To Max Tap</b>	<b>1/0 - 1/0 Str AL CU</b>
<b>Min Run To Min Tap</b>	<b>2 - 10 Str AL CU</b>
<b>Max Run To Min Tap</b>	<b>1/0 - 10 Str AL CU</b>
<b>Min Equal Run - Tap</b>	<b>4 - 4 Str AL CU</b>
<b>4</b>	<b>Spacer Electrolytical Copper</b>
<b>3</b>	<b>Nut Bronze</b>
<b>2</b>	<b>Rider Bronze</b>
<b>1</b>	<b>Body Electrolytical Copper</b>

