



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## N2 #2 STR Cu Split Bolt

Nsi Industries

Catalog Number	N2
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #6 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, #2 Awg (Range Of Equal Main and Tap-Stranded);#14 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 1.153 In Overall Length, Split Terminal, 600 V, 0.13 LB/Ea
Weight per unit	0.1300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	6 SOL - 2 STR
Wire Type	Class A & B

### Material, Color, and Finish

Color	Copper
Finish	COPPER

### Dimensions and Weight

Size	L=1.153 - W=.748
------	------------------

### Descriptions

Description	#2 STR CU SPLIT BOLT
extra long description	NSI N-2 12 Ton Compression Tool for
Features	Copper Split Bolt Connector 2 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

### Manufacturer Information

GTIN	00662381020055
UPC	662381020055

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Copper Split Bolts



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	40
Weight Per each	0.13

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C