



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N2 #2 STR Cu Split Bolt

Nsi Industries

Catalog Number	N2
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #6 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, #2 Awg (Range Of Equal Main and Tap-Stranded);#14 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 1.153 In Overall Length, Split Terminal, 600 V, 0.13 LB/Ea
Weight per unit	0.1300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	6 SOL - 2 STR
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER

Dimensions and Weight

Size	L=1.153 - W=.748
------	------------------

Descriptions

Description	#2 STR CU SPLIT BOLT
extra long description	NSI N-2 12 Ton Compression Tool for
Features	Copper Split Bolt Connector 2 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

Manufacturer Information

GTIN	00662381020055
UPC	662381020055

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Copper Split Bolts



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	40
Weight Per each	0.13

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C