



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## N20 2/0 Cu Split Bolt

*Nsi Industries*

Catalog Number	N20
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #2 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, 2/0 Awg (Range Of Equal Main and Tap-Stranded);#14 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 1.574 In Overall Length, Split Terminal, 600 V, 0.28 LB/Ea
Weight per unit	0.2800 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	2 SOL - 2/0 STR
Wire Type	Class A & B

### Material, Color, and Finish

Color	Copper
Finish	COPPER

### Dimensions and Weight

Size	L=1.574 - W=.866
------	------------------

### Descriptions

Description	2/0 CU SPLIT BOLT
extra long description	NSI N-2/0 Split Bolt Copper 2/0
Features	Copper Split Bolt Connector 2/0 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

### Manufacturer Information

GTIN	00662381020079
UPC	662381020079



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS

Type ..... Copper Split Bolts

## Packaging

Carton ..... 1

Package ..... 15

Weight Per each ..... 0.28

## Uses, Certifications, and Standards

Application ..... Wire Termination

environmental conditions ..... 90 C

standard ..... UL486B

Temperature Rating ..... 90 C