



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **N4 #4 Cu Split Bolt** *Nsi Industries*

Catalog Number	N4
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #8 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, #4 Awg (Range Of Equal Main and Tap-Stranded);#16 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper;Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 1.153 In Overall Length, Split Terminal, 600 V, 0.08 LB/Ea
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	8 SOL - 4 SOL
Wire Type	Class A & B

### **Material, Color, and Finish**

Color	Copper
Finish	COPPER

### **Dimensions and Weight**

Size	L=1.153 - W=.748
------	------------------

### **Descriptions**

Description	#4 CU SPLIT BOLT
extra long description	NSI N-4 Split Bolt Copper 4
Features	Copper Split Bolt Connector 4 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

### **Manufacturer Information**

GTIN	00662381020031
UPC	662381020031

### **Taxonomies, Classifications, and Categories**

Category Description	SPLIT BOLTS
Type	Copper Split Bolts



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	75
Weight Per each	0.08

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C