



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N4SP 4 Awg All Purpose Split Bolt

Nsi Industries

Catalog Number	N4SP
Manufacturer	Nsi Industries
Description	Compression Split Bolt Connector, #10 Awg (Stranded and Solid) Conductor Size, #6 Awg (Stranded) Conductor Size, Non-Insulated, Copper;Aluminum;Acsr Conductor Material, 2 Conductors, +90 °C Operating Temperature, 1.161 In Overall Length, Split Terminal, 600 V, 0.09 LB/Ea
Weight per unit	0.0900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	10 STR - 6 STR
Wire Type	Class A & B

Material, Color, and Finish

Color	Tin Plated Copper
Finish	Tin Plated Copper

Dimensions and Weight

Size	L=1.161 - W=.708
------	------------------

Descriptions

Description	4 AWG ALL PURPOSE SPLIT BOLT
extra long description	NSI N-4SP Split Bolt Copper 4 Tin P
Features	All Purpose Split Bolt Connector 4 AWG: All Purpose Split Bolt Connectors are used for combinations of aluminum to copper, aluminum to aluminum, steel to aluminum, copper to copper, and steel to copper applications. They have an electro-tinned body. UL listed for copper and copperweld wires only. Includes nut, spacer and pressure pad.

Manufacturer Information

GTIN	00662381020338
UPC	662381020338

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Tin Plated Copper Split Bolt



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.09

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C