

NEER Service Entrance Flashings


NC: No Caulk, Galvanized Steel




Applications

- These are used to provide a watertight connection between the roof line and ventilation pipes.

Standard Material

- NC and 1000: galvanized steel
- 1000-N: neoprene



	Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
			A	B
NC: No Caulk, Galvanized				
	1-1/4 - 1-1/2	NC-1069	8.75/222.3	12.50/317.5
	2	NC-1070	8.88/225.6	12.50/317.5
	2-1/2 - 3-1/2	NC-1071	10.75/273.1	14.50/368.3
1000: Galvanized with Collar				
	2	1070	10.75/273.1	14.50/368.3
	2-1/2	1071	10.75/273.1	14.50/368.3
1000-N: All-Neoprene				
	1-1/4 - 1-1/2	1069-N	9.00/228.6	11.25/285.8
	2	1070-N	9.00/228.6	11.50/292.1
	2-1/2 - 3-1/2	1071-N	9.00/228.6	11.50/292.1
	3	1072-N	10.00/254.0	13.50/342.9

NEER Service Entrance Flashings


NC: No Caulk, Galvanized Steel




Applications

- These are used to provide a watertight connection between the roof line and ventilation pipes.

Standard Material

- NC and 1000: galvanized steel
- 1000-N: neoprene



	Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
			A	B
	NC: No Caulk, Galvanized			
	1-1/4 - 1-1/2	NC-1069	8.75/222.3	12.50/317.5
	2	NC-1070	8.88/225.6	12.50/317.5
	2-1/2 - 3-1/2	NC-1071	10.75/273.1	14.50/368.3
	1000: Galvanized with Collar			
	2	1070	10.75/273.1	14.50/368.3
	2-1/2	1071	10.75/273.1	14.50/368.3
	1000-N: All-Neoprene			
	1-1/4 - 1-1/2	1069-N	9.00/228.6	11.25/285.8
	2	1070-N	9.00/228.6	11.50/292.1
	2-1/2 - 3-1/2	1071-N	9.00/228.6	11.50/292.1
	3	1072-N	10.00/254.0	13.50/342.9