



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NLOPACR6509T2430 6" 16.5W Led Disk LT 30K WHT 1100LM

*Nora Lighting, Inc.*

Catalog Number	NLOPACR6509T2430
Manufacturer	Nora Lighting, Inc.
Description	6" Ac Opal Led Surface Mount Fixtures Are Designed to Install Over A Standard Junction Box or Retrofit Over 5" or 6" Recessed Housings. The Low Profile Dimmable Luminaire Produces Even Illumination In Dedicated CCT Options. Input Voltage: 120VAC Lumens / Wattage: 1150LM / 16.5W Color Temperature: 3000K Color Rendering Index: 90+ Cri Dimming: Triac or Elv Finish: White Listing: Cetlus Listed For Wet Locations
Weight per unit	0.6000 (lbs/each)
Product Category	Lighting

### Features

Category	Flush Mounts
Safety Rating	Wet

### Material, Color, and Finish

Finish	white
Style	Contemporary Modern

### Descriptions

Description	6" 16.5W LED DISK LT 30K WHT 1100LM
Long Description	6" AC Opal LED surface mount fixtures are designed to install over a standard junction box or retrofit over 5" or 6" recessed housings. The low profile dimmable luminaire produces even illumination in dedicated CCT options. Input Voltage: 120VAC Lumens / Wattage: 1150lm / 16.5W Color Temperature: 3000K Color Rendering Index: 90+ CRI Dimming: Triac or ELV Finish: White Listing: cETLus Listed for Wet Locations
Product Type	Led Surface Mount

### Manufacturer Information

Brand	Nora Lighting
Manufacturers Part Number	NLOPAC-R6509T2430W

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Slimline/Low Profile

### Packaging

Carton	1
Weight Per each	0.6