



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NLOPACR6509T2430 6" 16.5W Led Disk LT 30K WHT 1100LM

Nora Lighting, Inc.

Catalog Number	NLOPACR6509T2430
Manufacturer	Nora Lighting, Inc.
Description	6" Ac Opal Led Surface Mount Fixtures Are Designed to Install Over A Standard Junction Box or Retrofit Over 5" or 6" Recessed Housings. The Low Profile Dimmable Luminaire Produces Even Illumination In Dedicated CCT Options. Input Voltage: 120VAC Lumens / Wattage: 1150LM / 16.5W Color Temperature: 3000K Color Rendering Index: 90+ Cri Dimming: Triac or Elv Finish: White Listing: Cetlus Listed For Wet Locations
Weight per unit	0.6000 (lbs/each)
Product Category	Lighting

Features

Category	Flush Mounts
Safety Rating	Wet

Material, Color, and Finish

Finish	white
Style	Contemporary Modern

Descriptions

Description	6" 16.5W LED DISK LT 30K WHT 1100LM
Long Description	6" AC Opal LED surface mount fixtures are designed to install over a standard junction box or retrofit over 5" or 6" recessed housings. The low profile dimmable luminaire produces even illumination in dedicated CCT options. Input Voltage: 120VAC Lumens / Wattage: 1150lm / 16.5W Color Temperature: 3000K Color Rendering Index: 90+ CRI Dimming: Triac or ELV Finish: White Listing: cETLus Listed for Wet Locations
Product Type	Led Surface Mount

Manufacturer Information

Brand	Nora Lighting
Manufacturers Part Number	NLOPAC-R6509T2430W

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Slimline/Low Profile

Packaging

Carton	1
Weight Per each	0.6