

# **A** Arlington

## **Part : NMLT90200**

Description: 90&deg; Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.633 lbs/each

Height: 5.320"

Width: 5.062"

Additional Color Options:  height="16" width="16"

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 2"

Trade Size: 2"

## **Packaging**

Unit: 2 pcs

Standard: 10 pcs



# **A** Arlington

## **Part : NMLT90200**

Description: 90&deg; Non-Metallic Connector

Listing: ULCSA

Country of Origin: USA

Weight: 0.633 lbs/each

Height: 5.320"

Width: 5.062"

Additional Color Options:  <http://www.aifittings.com/catalog/images/colors/black.png> height="16" width="16"

Material(s): UV Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 2"

Trade Size: 2"

## **Packaging**

Unit: 2 pcs

Standard: 10 pcs

