



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NP0DMDXWH Low Voltage Multi Option Dimmer

Lithonia Lighting

Catalog Number	NP0DMDXWH
Manufacturer	Lithonia Lighting
Description	The Npodm DX Is A Single Gang Decorator Style Toggle and/or Dimming Wall Switch That Provides Control Of Lighting In A Space Featuring Soft-Click Buttons and The Ability to Adjust The Level Of Any Nlight Controlled Dimmable Lighting
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Dimmers

Features

average life	87,600
dimmable	Yes
Hardware	Yes
Material	Plastic
Maximum Operating Temperature	60
Voltage Rating	Low Voltage
Warranty	5

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Height	5
Length	3.5
Width	2.5

Descriptions

Description	LOW VOLTAGE MULTI OPTION DIMMER
extra long description	LITH NPODM DX WH Low Voltage Push-B
Long Description	The nPODM DX is a single gang decorator style toggle and/or dimming wall switch that provides control of lighting in a space featuring soft-click buttons and the ability to adjust the level of any nLight controlled dimmable lighting
Product Type	Switch

Manufacturer Information

Brand	SENSOR SWITCH
GTIN	00745977903502
Manufacturers Part Number	NPODM DX WH
UPC	745977903502

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
----------------------	-----------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	0.5
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Manufacturing, Offices & Banks, Retail, Sports and Recreation, Warehouses
environmental conditions	Indoor
Mounting	SURFACE
standard	C-UL-US, UL DLC Standard, ROHS