



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NTCC125 1-1/4" Rigid Threadless Raintight Coupling *Appleton/Oz Gedney*

Catalog Number	NTCC125
Manufacturer	Appleton/Oz Gedney
Description	Coupling, Trade Size: 1-1/4 In, Outside Diameter: 2.31 In, Length: 2.88 In, Flexibility: Rigid and Imc, Material: Steel and Malleable Iron, Connection: Compression, Standard: UI 514B, UI File Number E11853, Nema FB-1, For Joining Lengths Of Steel Emt to Rigid Metal Conduit or Imc
Weight per unit	0.9600 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Compression
outside diameter	2.31

Dimensions and Weight

Length	2.88
--------	------

Descriptions

Description	1-1/4" RIGID THREADLESS RAIN TIGHT COUPLING
extra long description	APP NTCC-125 1-1/4 IN CPLG NO THRD
Long Description	Coupling, Trade Size: 1-1/4 IN, Outside Diameter: 2.31 IN, Length: 2.88 IN, Flexibility: Rigid And IMC, Material: Steel And Malleable Iron, Connection: Compression, Standard: UL 514B, UL File Number E11853, NEMA FB-1, For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
Product Type	1-1/4 In CPLG No THRD RGD Cond
Special Features	Threadless, Concretetight

Manufacturer Information

Brand	Appleton
GTIN	00781381638357
Manufacturers Part Number	NTCC-125
UPC	781381638357

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	COUPLING

Trade Size

Trade Size	1-1/4
------------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Package	25
Weight Per each	0.96

Uses, Certifications, and Standards

Application	For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
standard	UL 514B, UL File Number E11853, NEMA FB-1