



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTCC200 2" Rigid Threadless Raintight Coupling

*Appleton/Oz Gedney*

Catalog Number	NTCC200
Manufacturer	Appleton/Oz Gedney
Description	Coupling, Trade Size: 2 In, Outside Diameter: 3-1/4 In, Length: 4.06 In, Flexibility: Rigid and Imc, Material: Malleable Iron, Connection: Compression, Standard:UL 514B, UI File Number E11853, Nema FB-1, For Joining Lengths Of Steel Emt to Rigid Metal Conduit or Imc
Weight per unit	2.7 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Compression
outside diameter	3-1/4

### Dimensions and Weight

Length	4.06
--------	------

### Descriptions

Description	2" RIGID THREADLESS RAIN TIGHT COUPLING
extra long description	APP NTCC-200 2 IN CPLG NO THRD RGD
Long Description	Coupling, Trade Size: 2 IN, Outside Diameter: 3-1/4 IN, Length: 4.06 IN, Flexibility: Rigid And IMC, Material: Malleable Iron, Connection: Compression, Standard:UL 514B, UL File Number E11853, NEMA FB-1, For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
Product Type	2 In CPLG No THRD RGD Cond
Special Features	Threadless, Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00781381638456
Manufacturers Part Number	NTCC-200
UPC	781381638456

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	COUPLING

### Trade Size

Trade Size	2
------------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Weight Per each	2.7

## Uses, Certifications, and Standards

Application	For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
standard	UL 514B, UL File Number E11853, NEMA FB-1