



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTCC50 1/2" Rigid Threadless Raintight Coupling

*Appleton/Oz Gedney*

Catalog Number	NTCC50
Manufacturer	Appleton/Oz Gedney
Description	Coupling, Trade Size: 1/2 In, Outside Diameter: 1.31 In, Length: 2.13 In, Flexibility: Rigid and Imc, Material: Steel, Connection: Compression, Standard: UI 514B, UI File Number E11853, Nema FB-1, For Joining Lengths Of Steel Emt to Rigid Metal Conduit or Imc
Weight per unit	0.2200 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Compression
outside diameter	1.31

### Dimensions and Weight

Length	2.13
--------	------

### Descriptions

Description	1/2" RIGID THREADLESS RAIN TIGHT COUPLING
extra long description	APP NTCC-50 1/2 IN CPLG NO THRD RGD
Long Description	Coupling, Trade Size: 1/2 IN, Outside Diameter: 1.31 IN, Length: 2.13 IN, Flexibility: Rigid And IMC, Material: Steel, Connection: Compression, Standard: UL 514B, UL File Number E11853, NEMA FB-1, For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
Product Type	1/2 In CPLG No THRD RGD Cond
Special Features	Threadless, Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00781381638203
Manufacturers Part Number	NTCC-50
UPC	781381638203

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	COUPLING

### Trade Size

Trade Size	1/2
------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	100
Weight Per each	0.22

## Uses, Certifications, and Standards

Application	For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
standard	UL 514B, UL File Number E11853, NEMA FB-1