



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTL885TRBKCC6 Radiant Nlite/2 15A TR Outlts + Louv BK *Pass & Seymour/Legrand*

Catalog Number	NTL885TRBKCC6
Manufacturer	Pass & Seymour/Legrand
Description	15A 125V Tamper-Resistant Duplex Outlet With Led Night Light, Black
Weight per unit	0.2800 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
Contact Configuration	15A
Contact Rating	125
operating cycles	50,000 cycles minimum, resistive, inductive, tungstun filament lamp load
Voltage Rating	125

### Dimensions and Weight

Size	Depth 1.5" x Width 1.6" x Height 2.75"
------	--

### Descriptions

Description	RADIANT NLITE/2 15A TR OUTLTS + LOUV BK
extra long description	P&S NTL885TRBKCC6 RADIANT NLITE/2 1
Long Description	15A 125V Tamper-Resistant Duplex Outlet with LED Night Light, Black
Product Type	Radiant Nlite/2 15A TR Outlts + Louv BK
Special Features	This night light features five adjustable light levels (including OFF) and an optional louver for additional light-level control.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007032383
Manufacturers Part Number	NTL885TRBKCC6
UPC	785007032383

### Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Night Light w/Duplex Outlet

### Packaging

Carton	1
Package	6
Weight Per each	0.28



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	cULus, UL Listed