



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NTL885TRNICC6 Radiant Nlite/2 15A TR Outlts + Louv Ni *Pass & Seymour/Legrand*

Catalog Number	NTL885TRNICC6
Manufacturer	Pass & Seymour/Legrand
Description	15A 125V Tamper-Resistant Duplex Outlet With Led Night Light, Nickel Finish
Weight per unit	0.2800 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
Contact Configuration	15A
Contact Rating	125
operating cycles	50,000 cycles minimum, resistive, inductive, tungstun filament lamp load
Voltage Rating	125

Dimensions and Weight

Size	Depth 1.5" x Width 1.6" x Height 2.75"
------	--

Descriptions

Description	RADIANT NLITE/2 15A TR OUTLTS + LOUV NI
extra long description	P&S NTL885TRNICC6 RADIANT NLITE/2 1
Long Description	15A 125V Tamper-Resistant Duplex Outlet with LED Night Light, Nickel Finish
Product Type	Radiant Nlite/2 15A TR Outlts + Louv Ni
Special Features	This night light features five adjustable light levels (including OFF) and an optional louver for additional light-level control.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007032369
Manufacturers Part Number	NTL885TRNICC6
UPC	785007032369

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Night Light w/Duplex Outlet

Packaging

Carton	1
Package	6
Weight Per each	0.28



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	cULus, UL Listed