



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P1014RL Pan-Term® P10-14R-L Ring *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | P1014RL |
| Manufacturer | Panduit Corporation |
| Description | The P10-14R-L Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | None |
| Material | Copper |
| media | Yes |
| Voltage Rating | 2000 |
| Wire Size | #10 |

Material, Color, and Finish

| | |
|--------|--------|
| Finish | Tinned |
|--------|--------|

Dimensions and Weight

| | |
|------|------|
| Size | 1/4" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | PAN-TERM® P10-14R-L RING |
| extra long description | PAN P10-14R-L Pan-Term® P10-14R-L R |
| Long Description | The P10-14R-L Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® P10-14R-L Ring Terminal, Bare, 10-14 Awg, 1/4" Stu |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983802340 |
| Manufacturers Part Number | P10-14R-L |
| UPC | 074983802340 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Ring Terminal

Packaging

Carton 50

Package 500

Weight Per each 0.26

Uses, Certifications, and Standards

Enclosure Ring shape

Mounting 9/32

standard UL Listed 587H E52164, CSA Certified LR31212

Temperature Rating 302 Degrees Fahrenheit (150 Degrees Celsius)