



Incandescent Invite Bath & Vanity

	Туре	
	-09	-20
P2041		
P2078		
P2079		
P2080		
P2081		

Finish

		Antique		Dimensions (Inches)			
	Nickel	Bronze	Lamping	Α	В	c	D
P2041	-09	-20	1-100w (m)	6-1/2	11-1/2	8-1/4	3-3/4
P2078	-09	-20	2-100w (m)	14-1/2	7-3/8	7-1/2	4-7/8
P2079	-09	-20	3-100w (m)	23-1/2	7-3/8	7-1/2	4-7/8
P2080	-09	-20	4-100w (m)	32-1/2	7-3/8	7-1/2	4-7/8
P2081	-09	-20	5-100w (m)	41-1/2	7-3/8	7-1/2	4-7/8





Specifications:

General

- Silk mylar shade with Etched glass diffuser
- Plated Brushed Nickel (-09) finish
- Painted Antique Bronze (-20) finish
- Steel construction
- Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, fixtures are available

Mounting

- Wall mount
- Back plate covers a standard 4" hexagonal recessed outlet box

P2041: 4-3/4" W.

P2078, P2079, P2080, P2081: 7-1/2" W.

- Mounting strap for outlet box included
- Threaded socket ring secures glass

Electrical

- Medium base ceramic socket
- 6" of wire supplied
- Pre-wired

Labeling

• UL-CUL listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607