



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **P23I Wallplate, 2-G, 2) Box MT Blank, Iv** *Hubbell Wiring Devices*

Catalog Number	P23I
Manufacturer	Hubbell Wiring Devices
Description	Wallplate, 2-Gang, 2 Box Mount Blank, Ivory
Weight per unit	0.0350 (lbs/each)
Product Category	Wiring Devices

### **Features**

cutout	Blank Box Mount
orientation	Vertical
pallet quantity	11200

### **Dimensions and Weight**

Size	4.63 in x 4.69 in x 0.25 in
------	-----------------------------

### **Descriptions**

Description	WALLPLATE, 2-G, 2) BOX MT BLANK, IV
extra long description	HWDK P23I WALLPLATE, 2-G, 2) BOX MT
Features	Hubbell's line of polycarbonate wallplates features larger standard sized wallplates to provide extra coverage to hide rough box opening, improved aesthetics, greater strength, impact resistance, along with easy to clean finish in all different types of environments. Hubbell's standard sized wallplates are 1/8 inch larger to provide you that extra coverage to hide rough box openings. The depth is ¼ inch so that it will comfortably fit over the device even on imperfect installations or on retrofit work.
Long Description	Wallplate, 2-Gang, 2 Box Mount Blank, Ivory
Product Type	Wallplate, 2-G, 2) Box MT Blank, Iv
Special Features	Smooth Satin Finish

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778311765
Manufacturers Part Number	P23I
UPC	883778311765

### **Taxonomies, Classifications, and Categories**

Category Description	Residential plates
Type	Blank Box Mount

### **Packaging**

Carton	1
Package	25
Weight Per each	0.035



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	For use with Receptacle .....
Mounting .....	Painted Steel .....