

★ Swirled Alabaster Glass

SATIN SWIRLED GLASS WITH SUBTLY DECORATED TRIM
DAMP LOCATION LISTED.

Product No.	Finish	Description	Size	Lamp(s)
P3688-09	Brushed Nickel	One-light	11-1/2" dia., 3-3/4" ht.	1 medium base, 60w max.
P3688-15	Polished Chrome			
P3688-20	Antique Bronze			
P3688-30	Textured White			
P3689-09	Brushed Nickel	Two-light	14" dia., 4-3/4" ht.	2 medium base, each 60w max.
P3689-15	Polished Chrome			
P3689-20	Antique Bronze			
P3689-30	Textured White			
P3697-09	Brushed Nickel	Three-light	17-1/2" dia., 5-7/8" ht.	3 medium base, each 60w max.
P3697-15	Polished Chrome			
P3697-20	Antique Bronze			
P3697-30	Textured White			



★ Clear & White Glass

Product No.	Finish	Description	Size	Lamp(s)
P3348-30	White	Two-light	8-1/2" dia., 5-1/4" ht.	2 medium base, each 60w max.
P3350-30	White			



★ White Glass

WHITE GLASS BOWL WITH WHITE TRIM.

Product No.	Finish	Description	Size	Lamp(s)
P3516-30	White	One-light	6-3/4" dia., 4-3/4" ht.	1 medium base, 60w max.
P3518-30	White			
P3520-30	White	Two-light	10-3/4" dia., 5-3/8" ht.	2 medium base, each 75w max.



★ Swirled Alabaster Glass

SATIN SWIRLED GLASS WITH SUBTLY DECORATED TRIM
DAMP LOCATION LISTED.

Product No.	Finish	Description	Size	Lamp(s)
P3688-09	Brushed Nickel	One-light	11-1/2" dia., 3-3/4" ht.	1 medium base, 60w max.
P3688-15	Polished Chrome			
P3688-20	Antique Bronze			
P3688-30	Textured White			
P3689-09	Brushed Nickel	Two-light	14" dia., 4-3/4" ht.	2 medium base, each 60w max.
P3689-15	Polished Chrome			
P3689-20	Antique Bronze			
P3689-30	Textured White			
P3697-09	Brushed Nickel	Three-light	17-1/2" dia., 5-7/8" ht.	3 medium base, each 60w max.
P3697-15	Polished Chrome			
P3697-20	Antique Bronze			
P3697-30	Textured White			



★ Clear & White Glass

Product No.	Finish	Description	Size	Lamp(s)
P3348-30	White	Two-light	8-1/2" dia., 5-1/4" ht.	2 medium base, each 60w max.
P3350-30	White	Two-light	10-1/2" dia., 5-1/4" ht.	2 medium base, each 75w max.



★ White Glass

WHITE GLASS BOWL WITH WHITE TRIM.

Product No.	Finish	Description	Size	Lamp(s)
P3516-30	White	One-light	6-3/4" dia., 4-3/4" ht.	1 medium base, 60w max.
P3518-30	White	Two-light	8-3/4" dia., 5" ht.	2 medium base, each 60w max.
P3520-30	White	Two-light	10-3/4" dia., 5-3/8" ht.	2 medium base, each 75w max.

