

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3817-09

Melon

Two-light close-to-ceiling with etched ribbed melon glass with center lock up in Brushed Nickel finish.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched ribbed glass bowl



Diameter: 13-1/4"

Height: 7"

Glass: 9-13/16" dia.

Height: 4-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling flush mounted</p> <p>Mounting strap for outlet box included</p> <p>Ceiling pan covers a standard 4" hexagonal recessed outlet box</p> <p>13-1/4" dia., 1-5/8"</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p>	<p>Quantity: 2</p> <p>75W Medium Base</p> <p>Medium sockets</p>	<p>cCSAus Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p>

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3817-09

Melon

Two-light close-to-ceiling with etched ribbed melon glass with center lock up in Brushed Nickel finish.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: Etched ribbed glass bowl



Diameter: 13-1/4"

Height: 7"

Glass: 9-13/16" dia.

Height: 4-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" hexagonal recessed outlet box 13-1/4" dia., 1-5/8"	Pre-wired 6" of wire supplied 120V	Quantity: 2 75W Medium Base Medium sockets	cCSAus Damp location listed 1 year warranty Companion fixtures are available