

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P3817-09

## Melon

Two-light close-to-ceiling with etched ribbed melon glass with center lock up in Brushed Nickel finish.

**Category:** Close-to-Ceiling

**Finish:** Brushed Nickel (plated)

**Construction:** Steel construction

**Glass:** Etched ribbed glass bowl



**Diameter:** 13-1/4"

**Height:** 7"

**Glass:** 9-13/16" dia.

**Height:** 4-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" hexagonal recessed outlet box 13-1/4" dia., 1-5/8"	Pre-wired 6" of wire supplied 120V	Quantity: 2 75W Medium Base Medium sockets	cCSAus Damp location listed 1 year warranty Companion fixtures are available

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P3817-09

## Melon

Two-light close-to-ceiling with etched ribbed melon glass with center lock up in Brushed Nickel finish.

**Category:** Close-to-Ceiling

**Finish:** Brushed Nickel (plated)

**Construction:** Steel construction

**Glass:** Etched ribbed glass bowl



**Diameter:** 13-1/4"

**Height:** 7"

**Glass:** 9-13/16" dia.

**Height:** 4-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" hexagonal recessed outlet box 13-1/4" dia., 1-5/8"	Pre-wired 6" of wire supplied 120V	Quantity: 2 75W Medium Base Medium sockets	cCSAus Damp location listed 1 year warranty Companion fixtures are available