

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3925-09

Melon

Two-light flush mount with dome shaped alabaster glass, solid trim and decorative knobs. Center lock-up with matching finial.

- Brushed Nickel finish.
- Alabaster Glass.
- Decorative details.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel construction

Glass/Shade: Alabaster glass bowl



Diameter: 13-1/4"

Height: 5-7/8"

Glass

Width: 9-13/16"

Height: 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling flush mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" octagonal recessed outlet box	Pre-wired 6" of wire supplied 120 V	Quantity: Two 75w max. Medium Base E26 base ceramic sockets	cCSAus Damp location listed 1 year warranty

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3925-09

Melon

Two-light flush mount with dome shaped alabaster glass, solid trim and decorative knobs. Center lock-up with matching finial.

- Brushed Nickel finish.
- Alabaster Glass.
- Decorative details.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel construction

Glass/Shade: Alabaster glass bowl



Diameter: 13-1/4"

Height: 5-7/8"

Glass

Width: 9-13/16"

Height: 3-9/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling flush mounted</p> <p>Mounting strap for outlet box included</p> <p>Ceiling pan covers a standard 4" octagonal recessed outlet box</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Two 75w max. Medium Base</p> <p>E26 base ceramic sockets</p>	<p>cCSAus Damp location listed</p> <p>1 year warranty</p>