



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P400311A 18/4 Awg, CMP/CL3P Plenum Rated, Non-Shielded *Southwire Company*

| | |
|------------------|--|
| Catalog Number | P400311A |
| Manufacturer | Southwire Company |
| Description | 18 Awg 4/C Stranded Unshielded CMP/CL3P/FPLP Cable |
| Weight per unit | 0.0370 (lbs/each) |
| Product Category | 20170112081814 |

Features

| | |
|----------------------|------------|
| amperage rating | CL3 |
| Conductor Size | 18 |
| core | UNSHIELDED |
| Number of Conductors | 4 |
| outside diameter | 0.196 |
| Resistance | 6.92 |
| strands | 7 |
| Voltage Rating | 300 |

Material, Color, and Finish

| | |
|---------------------|--------|
| Color | White |
| Conductor Material | BC |
| Finish | BULK |
| Insulation Material | LS-PVC |
| Jacket Material | LS-PVC |

Descriptions

| | |
|------------------------|--|
| Construction | CABLE |
| Description | 18/4 AWG, CMP/CL3P PLENUM RATED, NON-SHIELDED |
| extra long description | SWC P40031-1A 18 AWG 4/C STRANDED U |
| Long Description | 18 AWG 4/C STRANDED UNSHIELDED CMP/CL3P/FPLP CABLE |
| Product Type | 18 Awg 4/C Stranded Unshielded CMP/CL3P/FPLP Cable |
| Special Features | CL3P |

Manufacturer Information

| | |
|---------------------------|-------------------|
| Brand | SOUTHWIRE COMPANY |
| GTIN | 00032886881749 |
| Manufacturers Part Number | P40031-1A |
| UPC | 032886881749 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | CMP |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1000 |
| Weight | 30 |
| Weight Per each | 0.037 |

Uses, Certifications, and Standards

| | |
|--------------------|--------|
| Application | CL3 |
| standard | UL 444 |
| Temperature Rating | 75 |