

Eaton P48G11S1526

Catalog Number: P48G11S1526

15 KVA Mini Power Center 1PH 480V-120/240V 26 spaces



General specifications

Product Name	Catalog Number
Eaton Mini-Power center	P48G11S1526
UPC	Product Length/Depth
786680225604	14.5 in
Product Height	Product Width
43.4 in	15.9 in
Product Weight	Warranty
425 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
NAFTA	IEEE Certified CSA Certified UL Listed ANSI

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 3R

Frame

287

Insulation

180 °C

Mounting

Wall Mount

Tap size

2 at -5% FCBN

Type

Mini-power center

Wiring connection

M48G11H

Performance Ratings

Frequency rating

60 Hz

kVA

15 kVA

Kva Rating

15 kVA

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Modification 1

NEMA 3R

Weathershield

Not required

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - P48G11S1526](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton P48G11S1526

Catalog Number: P48G11S1526

15 KVA Mini Power Center 1PH 480V-120/240V 26 spaces



General specifications

Product Name

Eaton Mini-Power center

Catalog Number

P48G11S1526

UPC

786680225604

Product Length/Depth

14.5 in

Product Height

43.4 in

Product Width

15.9 in

Product Weight

425 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

NAFTA

Certifications

IEEE Certified
CSA Certified
UL Listed
ANSI



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 3R

Frame

287

Insulation

180 °C

Mounting

Wall Mount

Tap size

2 at -5% FCBN

Type

Mini-power center

Wiring connection

M48G11H

Performance Ratings

Frequency rating

60 Hz

kVA

15 kVA

Kva Rating

15 kVA

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Modification 1

NEMA 3R

Weathershield

Not required

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - P48G11S1526](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia