



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P48G11S15P 15KVA Mini PWR CNTR 1PH 480V-120/240V

Eaton Corp

Catalog Number	P48G11S15P
Manufacturer	Eaton Corp
Description	Eaton Mini-Power Center, Mini-Power Center, Aluminum, Nema 3R, 286, 60 HZ, Single-Phase, 480 V, 120/240 V, 2 At -5% FCBN, 115 °C Rise, 15 Kva, Indoor-Outdoor, 107a15k
Weight per unit	212.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

dimensions	11.6000 IN X 13.1000 IN X 37.5000 IN
media	Yes
Phase	Single-phase

Descriptions

Description	15KVA MINI PWR CNTR 1PH 480V-120/240V
extra long description	ETN P48G11S15P Mini-Power Center, S
Features	Eaton's Mini-Power Center incorporates an encapsulated transformer, interior, primary and secondary main circuit breakers in to a single assembly. Mini-Power Centers are ideally suited for applications where 120 volts are required at a remote location, such us parking lots, workbenches, and temporary power on construction sites.
Long Description	Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K
Product Type	Mini-Power Center, Single-Phase, PV: 480

Manufacturer Information

Brand	Eaton
GTIN	00786680140228
Manufacturers Part Number	P48G11S15P
UPC	786680140228

Taxonomies, Classifications, and Categories

Category Description	Mini Power Centers
Type	Mini-power center

Packaging

Carton	1
Weight Per each	212



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Frequency Rating	60 Hz
Operating Temperature	115 °C rise
standard	IEEE Certified,ANSI,UL Listed,CSA Certified,NEMA Compliant