

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5745-31

Ceiling Mount

Two-light non-metallic ceiling light with one-piece white acrylic diffuser and scalloped detail.

Category: Outdoor

Finish: Black (painted)

Construction:

Glass: White acrylic diffuser



Diameter: 10-1/4"

Height: 5-1/2"

Glass: 8-3/4" SQ

Height: 4"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---|---|---|
| <p>Ceiling mounted</p> <p>Mounting strap for outlet box included</p> | <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p> | <p>Quantity: 2</p> <p>60W Medium Base</p> <p>Medium porcelain sockets</p> | <p>UL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p> |

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5745-31

Ceiling Mount

Two-light non-metallic ceiling light with one-piece white acrylic diffuser and scalloped detail.

Category: Outdoor

Finish: Black (painted)

Construction:

Glass: White acrylic diffuser



Diameter: 10-1/4"

Height: 5-1/2"

Glass: 8-3/4" SQ

Height: 4"

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---|---|---|
| <p>Ceiling mounted</p> <p>Mounting strap for outlet box included</p> | <p>Pre-wired</p> <p>6" of wire supplied</p> <p>120V</p> | <p>Quantity: 2</p> <p>60W Medium Base</p> <p>Medium porcelain sockets</p> | <p>UL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p> |