



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **P814RQ Pan-Term® P8-14R-Q Ring T** *Panduit Corporation*

Catalog Number	P814RQ
Manufacturer	Panduit Corporation
Description	The P8-14R-Q Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2000 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

connection	Standard
insulation	None
Material	Copper
media	Yes
Voltage Rating	2000
Wire Size	8

### **Material, Color, and Finish**

Finish	Tinned
--------	--------

### **Dimensions and Weight**

Size	1/4"
------	------

### **Descriptions**

Description	PAN-TERM® P8-14R-Q RING T
extra long description	PAN P8-14R-Q Pan-Term® P8-14R-Q Rin
Long Description	The P8-14R-Q Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® P8-14R-Q Ring Terminal, Bare, 8 Awg, 1/4" Stud, PK

### **Manufacturer Information**

Brand	Panduit®
GTIN	00074983870790
Manufacturers Part Number	P8-14R-Q
UPC	074983870790

### **Taxonomies, Classifications, and Categories**

Category Description	TERMINALS
Type	Ring Terminal



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	250
Weight Per each	0.2

## Uses, Certifications, and Standards

Enclosure	Ring shape
Mounting	3/8
standard	cULus Listed 587H E52164, CSA Certified LR31212
Temperature Rating	302 Degrees Fahrenheit (150 Degrees Celsius)