Specifications



Photo is representative

Eaton PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

General specifications	
PRODUCT NAME	Eaton B-Line series push button enclosures
CATALOG NUMBER	PB2M-4XS
UPC	782051138146
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	5.75 in
PRODUCT WIDTH	3.25 in
PRODUCT WEIGHT	2.1 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	Not Applicable



Material/finish	
MATERIAL	304 stainless steel

Model	
STYLE	Small single door

WALL THICKNESS	16 gauge
FINISH COLOR	#4 brushed
COLOR	Gray

MODEL	PBM4XS enclosure
COVER TYPE	Screw
MOUNTING METHOD	Surface
MOUNTING HOLE DETAILS	External mounting feet
SPECIAL FEATURES	Removable cover, recessed pull ring, s.s. screws

Standards		
NEMA RATING	4X	
COUNTRY OF ORIGIN	US	

Resources	
CATALOGS	Pushbutton-enclosure- operator.pdf
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PB2M-4XS

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc

© 2025 Eaton. All Rights

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







