




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PCMB14 46 to 90 Comb Numb BK *Panduit Corporation*

Catalog Number	PCMB14
Manufacturer	Panduit Corporation
Description	Stronghold PCMB-14 Pre-Printed Wire Marker Books Are Conveniently Pocket-Sized, Containing Wire Labels Printed On Vinyl Cloth. Markers Are Durable Enough For Up to 5 Years Outdoor Uv Resistance, Oil and Abrasions. They Can Also Be Torn In Half to Label Each End Of The Conductor. The Legend Includes 46-90, There Are 10 Markers Per Legend, and 10 Pages Per Book.
Weight per unit	1.0 (lbs/each)
Product Category	Markers & Marking Tapes

### Features

Legend	46 thru 90
Material	Vinyl Cloth
media	Yes
Wire Size	0.38

### Dimensions and Weight

Length	1.37
Size	0.22 x 1.56 es

### Descriptions

Description	46 TO 90 COMB NUMB BK
extra long description	PAN PCMB-14 StrongHold™ PCMB-14 Pre
Long Description	StrongHold PCMB-14 Pre-Printed Wire Marker Books are conveniently pocket-sized, containing wire labels printed on vinyl cloth. Markers are durable enough for up to 5 years outdoor UV Resistance, oil and abrasions. They can also be torn in half to label each end of the conductor. The legend includes 46-90, there are 10 markers per legend, and 10 pages per book.
Product Type	Stronghold™ PCMB-14 Pre-Printed Wire Marker Book, 14, Vinyl

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983948130
Manufacturers Part Number	PCMB-14
UPC	074983948130



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... WIRE LUBE, MARKERS, & TIES

Type ..... Pre-Printed Wire Marker Book

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 1

## Uses, Certifications, and Standards

standard ..... RoHS Compliant

Temperature Rating ..... 170