



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PDREPWH Caseta Repeater

Lutron

Catalog Number	PDREPWH
Manufacturer	Lutron
Description	Lutron Caseta Smart Wireless Repeater/Range Extender, White
Weight per unit	0.4300 (lbs/each)
Product Category	Line Construction Material

### Features

Material	Plastic
media	Yes
Voltage Rating	5

### Material, Color, and Finish

Color	White
Finish	Gloss

### Dimensions and Weight

Height	1.19
Length	2.75
Width	2.75

### Descriptions

Description	CASETA REPEATER
extra long description	LUT PD-REP-WH Cas ta Repeater/Range
Features	With the Caseta Smart Wireless Repeater by Lutron, you can now extend the range of your Caseta system up to 60 ft. Use the included power adapter to plug the repeater into an outlet within 60 ft. of your Caseta smart hub in room where coverage can be problematic - no extra ethernet connection required. This is ideal for homes that need extra range due to unique layouts, smart hubs that are not centrally located, or dense, concrete, or cement walls.
Long Description	Lutron Caseta Smart Wireless Repeater/Range Extender, White
Product Type	Cas Ta Repeater/Range Extender
Special Features	Expands RF range. Easily adds to an existing system through the Caséta App1 or system software . Can add one wireless repeater per system. Works with Caséta Wireless systems only

### Manufacturer Information

Brand	Lutron
GTIN	00784276274043
Manufacturers Part Number	PD-REP-WH
UPC	784276274043



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.43

## Uses, Certifications, and Standards

Application	Lighting and shade Control
Enclosure	Plastic
Frequency Rating	431 to 437
Mounting	Tabletop
standard	cULus Listed FCC approved IC certified IFETEL certified
Temperature Rating	32 to 104