



## PENE4

by Burndy  
Catalog ID: PENE4

Electrical sealing compound, Squeeze Bottle.

Features: PENETROX E Consists Of A Non-Petroleum Base Vehicle In Which Copper Granules Are Suspended, Recommended For Copper To Copper Applications, Grounding And For Use On Copper Conduit Threads, UL Listed, Pour Point(maximum): -10 DEG F, Dropping Point (minimum): 500 DEG F, Penetration (unworked): 250 In Accordance To ASTM D217, Container Consist Of: Non - Petroleum Base Vehicle In Which Copper Granules Are Suspended

## Product Details

### General

Application	For Copper To Copper
Application - For Use On	Copper to Copper
Container Type	Squeeze Bottle
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	E
UPC	781810593141
UPC 12 Digit	7818105931411
Viscosity at 100 Fahrenheit	250 °F

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Container Size	4 oz
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)