



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH250MLI CNTL XFMR 250VA 460/230/208-115/24 *Hammond Power Solutions*

Catalog Number	PH250MLI
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 460/230/208 PV, 115/24 SV, 250 Kva
Weight per unit	N/A
Product Category	Encapsulated Industrial Contro

Features

connection	Terminal Block
Input Voltage	480/240, 460/230/208, 440/220/200
Output Voltage	120/25, 115/24, 110/23
Phase	1 PH
Wattage	250 W

Dimensions and Weight

Height	4.44 in
Length	51894
Width	5.19 in

Descriptions

Description	CNTL XFMR 250VA 460/230/208-115/24
extra long description	HMND PH250MLI CNTL 250 VA460/230/2
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 460/230/208 PV, 115/24 SV, 250 kVA
Product Type	CNTL 250 VA460/230/208 50/60H
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	Hammond Power Solutions
Manufacturers Part Number	PH250MLI
sub brand	Machine Tool Industrial Control Transformer

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60 Hz
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum