



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PH250MLI CNTL XFMR 250VA 460/230/208-115/24 *Hammond Power Solutions*

Catalog Number	PH250MLI
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 460/230/208 PV, 115/24 SV, 250 Kva
Weight per unit	N/A
Product Category	Encapsulated Industrial Contro

### Features

connection	Terminal Block
Input Voltage	480/240, 460/230/208, 440/220/200
Output Voltage	120/25, 115/24, 110/23
Phase	1 PH
Wattage	250 W

### Dimensions and Weight

Height	4.44 in
Length	51894
Width	5.19 in

### Descriptions

Description	CNTL XFMR 250VA 460/230/208-115/24
extra long description	HMND PH250MLI CNTL 250 VA460/230/2
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 460/230/208 PV, 115/24 SV, 250 kVA
Product Type	CNTL 250 VA460/230/208 50/60H
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

### Manufacturer Information

Brand	Hammond Power Solutions
Manufacturers Part Number	PH250MLI
sub brand	Machine Tool Industrial Control Transformer

### Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

### Availability

Manufacturer Status	Inactive
---------------------	----------

### Packaging

Carton	1
Weight Per each	0



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60 Hz
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum